

Take 2 Adapter



A message-on-hold adapter that allows up to 2 calls to be placed on hold on a single, 2-line (non-KSU) telephone.

[Take 2 Adapter](#) is ideal for a small business that requires message-on-hold but has a standard telephone (no phone system). When combined with a message-on-hold device such as our [Messenger USB](#), Take 2 is an easy, economic solution for the small office/home office (SOHO) market.

How Does Take 2 Work?

When a call is placed on hold, press either the "1" (for a call on line 1) or "2" (for a call on line 2) button on the Take 2. The phone handset can then be placed back on the cradle or another line can be accessed. A blue LED light indicates which line is on hold. Press either the "1" or "2" button on the Take 2 to remove the call from hold. As Take 2 captures the phone line, it provides a reliable, secure connection, even with a cordless phone.

Who is the Ideal Take 2 User?

As Take 2 cannot transfer the hold connection from one Take 2 device to another, it is recommended for a small business that has a single (non-KSU) telephone with up to 2 phone lines. A few examples of this type of business are home-based businesses, florist shops, small real estate offices, gift shops, churches, beauty salons, spas and more.

What is Required to Use a Take 2?

An external audio source such as our [Messenger USB](#) is required to play message-on-hold audio. All cables, connectors & cords are packaged with the [Take 2](#), including a splitter and adapter for 2-line installations where both lines are on separate wires.

